

# SCHOTT N-WG280, 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock #16-403 3-5 DAYS

- 1 +

A\$51.20

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| A\$51.20                      |
| Qty 11+                       |
| A\$44.80                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

## Get Product Downloads

Diameter (mm):  
12.50

Cut-On Wavelength (nm):  
280.00 ±6

Density (g/cm³):

|                                                                |
|----------------------------------------------------------------|
| 2.51                                                           |
| <b>Glass/Filter Number:</b><br><a href="#">SCHOTT N-WG280</a>  |
| <b>Coating:</b><br>Uncoated                                    |
| <b>Color:</b><br>Clear                                         |
| <b>Passband Limit 1 <math>\lambda_{p1}</math> (nm):</b><br>380 |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.52           |
| <b>Spectral Transmittance <math>t_p</math> (%):</b><br>99      |
| <b>Stopband Limit <math>\lambda_s</math>(nm):</b><br>230       |
| <b>Surface Quality:</b><br>60-40                               |
| <b>Transformation Temperature (°C):</b><br>558                 |
| <b>Thickness (mm):</b><br>1.00 ±0.1                            |
| <b>Type:</b><br>Longpass Filter                                |
| <b>Wavelength:</b><br>UV                                       |
| <b>Dimensional Tolerance (mm):</b><br>±0.2                     |
| <b>Reflection Factor <math>P_d</math>:</b><br>0.92             |
| <b>Bevel:</b><br>Protective as needed                          |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
|------------------------------------------------------------|