

Stainless Steel Transmission Dip Probe Tip, 10 mm

See More by [Ocean Optics](#)



Stock #90-572 NEW 1 In Stock

-

1

+

A\$696⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$696.00 each
Need More?	Request Quote

Product Downloads

Stainless steel	Construction Material:
-----------------	------------------------

General

RT-10MM	Model Number:
---------	---------------

Optical Properties

200 - 2500	Wavelength Range (nm):
------------	------------------------

Regulatory Compliance

Compliant		RoHS 2015:
View		Certificate of Conformance:
Compliant		Reach 250:

Product Details

- Transmission Dip Probes Designed for Reliable In-Solution Absorbance/Transmission Measurements
- Rugged Stainless Steel or PEEK for Tough Process Conditions and Harsh Environments
- Flexible Path Lengths Available with Interchangeable Probe Tips
- Compatible with Ocean Optics Spectrometers and Accessories

Ocean Optics Transmission Dip Probes couple to spectrometers and light sources to measure absorbance and transmission in solutions. Choose from ruggedized high-pressure probe ([#90-569](#)) for demanding process environments or PEEK-jacketed probes ([#90-570](#) and [#90-571](#)) for harsh chemical conditions, spanning UV–VIS to VIS–NIR wavelengths. Easily customize your setup with accessories such as interchangeable probe tips in various path lengths and the protective sleeve ([#90-585](#)) for extended durability in corrosive or high-temperature applications. Ocean Optics Transmission Dip Probes are designed for seamless integration with [Ocean Optics spectroscopy systems and compatible accessories](#).