


[See all 3 Products in Family](#)

TECHSPEC® T-Mount Iris Diaphragm Mount



T-Mount Iris Diaphragm Mount, #52-299

Stock **#52-299 2 In Stock**

⊖ 1 ⊕ A\$361⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-4 | A\$361.60 each |
| Qty 5-9 | A\$319.04 each |
| Qty 10-25 | A\$294.40 each |
| Need More? | Request Quote |

Product Downloads

General

Iris Diaphragm **Function:**

Physical & Mechanical Properties

18.13 **Extension Length (mm):**

22.0 **Total Length (mm):**

1.2 - 30.0 Clear Aperture CA (mm):

58.0 Outer Diameter (mm):

Threading & Mounting

T-Mount Thread Type:

Regulatory Compliance

Compliant RoHS 2015:

Compliant Reach 219:

View Certificate of Conformance:

Product Details

- Variable Apertures for C, S, and T-Mount Systems
- Male and Female Thread at Opposite Ends for Easy Integration
- Adjusted via Rotating Ring or Lever for Precision Control

TECHSPEC® C, S, and T-Mount Iris Diaphragm Mounts feature iris diaphragms that allow for precision control over the internal aperture within a system. Using male and female threads, these mounts can be placed anywhere within a C, S, or T-Mount system. The apertures can be adjusted via a rotating ring for the C-Mount version, with a 4mm lever for the S-Mount version and with a 5mm lever for the T-Mount version. TECHSPEC C, S, and T-Mount Iris Diaphragm Mounts add 12mm, 12mm, and 18mm to the system length, respectively. These mounts are ideal for providing control over the $f\#$, field stop diameter, and overall energy throughput of a C, S, or T-Mount system.

NOTE: The iris planes sit approximately 15mm, 8mm, and 12mm from the female ends of the TECHSPEC C, S, and T-Mount Iris Diaphragm Mounts, respectively.

Technical Information

