

[See all 24 Products in Family](#)

# Ti:Sapphire Flat Top Beam Shaper | πShaper 6\_6\_TiS

See More by [AdlOptica](#)



Ti:Sapphire Flat Top Beam Shaper, #36-649

Stock **#36-649** 1 In Stock

-

1

+

A\$9,922<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | A\$9,922.00 each              |
| Qty 5-10       | A\$8,943.00 each              |
| Qty 11+        | A\$8,439.00 each              |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

πShaper 6\_6\_TiS

Model Number:

Beam Shaper

Type:

Flat Top

Style:

| Physical & Mechanical Properties      |                                                       |
|---------------------------------------|-------------------------------------------------------|
| 143.00                                | Length (mm):                                          |
| <270                                  | Weight (g):                                           |
| 39.00                                 | Diameter (mm):                                        |
| Optical Properties                    |                                                       |
| 6.4 - 6.5                             | Entrance Beam Diameter, 1/e <sup>2</sup> (mm):        |
| 800                                   | Design Wavelength DWL (nm):                           |
| 700 - 900                             | Wavelength Range (nm):                                |
| 20 mJ/cm <sup>2</sup> @ 5ns (typical) | Damage Threshold, By Design: <input type="checkbox"/> |
| 6.0                                   | Output Diameter, FWHM (mm):                           |
| 20 mJ/cm <sup>2</sup> @ 5ns (typical) | Damage Threshold, Pulsed:                             |
| Threading & Mounting                  |                                                       |
| M27 x 1                               | Mounting Threads:                                     |
| Regulatory Compliance                 |                                                       |
| Compliant                             | RoHS 2015:                                            |
| View                                  | Certificate of Conformance:                           |
| Compliant                             | Reach 250:                                            |

## Product Details

- Convert Gaussian Beam Profile to Flat Top Profile
- Near 100% Efficiency
- No Internal Focusing Enables High Power Laser Input
- [AdlOptica Focal-πShaper Q Flat Top Beam Shapers](#) Also Available

AdlOptica πShaper (piShaper) Flat Top Beam Shapers are refractive field mapping optical systems that convert collimated Gaussian input beams into collimated flat top beams with a uniform intensity distribution and flat phase front. Due to the field mapping optical design, the even intensity distribution of the converted beam is stable over great distances making it ideally suitable for holography, microscopy, and system integration. With no internal focusing, they are also the perfect solution in applications such as material micromachining, welding, and engraving that require high power lasers. These AdlOptica πShaper Flat Top Beam Shapers are offered in common YAG, fiber laser, and CO2 laser sources, operating over a defined wavelength range for laser tuning. Achromatic versions are designed to be used with multiple laser sources.

**Note:** Focusing a flat-top beam after a πShaper results in loss of the flat top profile. [AdlOptica Focal-πShaper Q Flat Top Beam Shapers](#) are available for applications that require a focused flat top spot.



## Technical Information

