

Tube Lens



Stock **#18-505** 12 In Stock

-

1

+

A\$832⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	A\$832.00 each
Qty 5+	A\$790.40 each
Need More?	Request Quote

Product Downloads

General

Note:

One required between camera tube and tube lens spacer/filter cube

Physical & Mechanical Properties

Length (mm):

16.15

Maximum Diameter (mm):

Optical Properties

	Focal Length FL (mm):
120.00	
	Magnification:
1X	

Threading & Mounting

	Mounting Threads:
M29 x 0.75 & Ø30mm Dovetail	

Regulatory Compliance


	Certificate of Conformance:
View	

Product Details

- Up to 43% Smaller than Industry Standard Systems
 - Optimized Performance up to 1.1" Sensor
 - Ideal for Life Science and Industrial Applications
 - Winner of the [2023 Bronze VSD Innovators Award](#)
- Edmund Optics® 120i Plan APO Infinity Corrected Objectives are infinite conjugate microscope objectives that offer exception image flatness and chromatic correction over 400-700nm. These objectives were designed for a 1.1" sensor to offer a large field of view and reliable image quality for high-throughput imaging applications. Ideal for life science and machine vision applications such as microscopy, flow cytometry, pharmaceutical inspection, and assembly line or fault inspection.
- These objectives won the [2023 Bronze VSD Innovators Award](#).

Technical Information

Compact Tube Lens System



Standard Tube Lens System

