

VZM i-Series Zoom Lock Adapter



VZM™ 200i



+7

Stock #57-831 3 In Stock

-

1

+

A\$176⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$176.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Lens Accessory

Type:


Regulatory Compliance

PRODUCT DETAILS

- Designed to Accomodate up to 2/3" Sensor Size Formats
- Dependable, Versatile Performance in Compact Designs
- Analog and Digital **Imaging Systems** Available


VZM™ Zoom Imaging Lenses enable inspection of a wide range of objects without the inconvenience of changing working distances. In addition, the parfocal zoom allows magnifications to be easily changed without refocusing. These economical lenses are available in working distances ranging from 35mm to 175mm and offer a maximum 2/3" sensor format. Iris versions (i-series) all have locking iris, front filter thread, removable mounting flange, and optional zoom lock. All lenses have a 50mm diameter flange (removable on iris versions except 450i Right Angle) for mounting. VZM™ Zoom Imaging Lenses are ideal for inspection of integrated circuits and solder joints. Also suited for quality control and laboratory inspection needs, as well as surface analysis.

TECHNICAL INFORMATION




Depth of Field Curves
Video Zoom Microscope VZM 450

Depth of Field Line Profile @ 4.5X PMAG, 11 lp/mm



Depth of Field Line Profile @ 0.7X PMAG, 11 lp/mm










Modulation Transfer Function Curves
Video Zoom Microscope VZM 450



Modulation Transfer Function @ 4.5X PMAG

MTF NOT AVAILABLE FOR MICROSCOPE MAGNIFICATIONS

Modulation Transfer Function @ 0.7X PMAG







VZM Model	100i	200i	300	300i	450	450i	600i	1000	1000i
Zoom Ratio	4:1	4:1	4:1	4:1	6.4:1	6:1	6:1	4:1	4:1
Magnification	0.25 - 1X	0.5 - 2X	0.75 - 3X	0.75 - 3X	0.7 - 4.5X	0.75 - 4.5X	1 - 6X	2.5 - 10X	2.5 - 10X
Manual Iris	☐	☐		☐		☐	☐		☐
Rotatable Mount	☐	☐		☐		☐	☐		☐
Zoom Lock Adapter	☐	☐		☐		☐	☐		☐
Motorized Version			☐		☐			☐	
Right Angle Version						☐			

Primary Magnification	With 0.5X Lens	
	Minimum 0.25X	Maximum 1.0X
FOV (½" Horizontal Sensor)	24.0mm	6.0mm
Resolution in Object Space	10 lp/mm	40 lp/mm
Resolution in Image Space	40 lp/mm	40 lp/mm
Working Distance (±3mm)	152mm	152mm

Primary Magnification	With 0.5X Lens	
	Minimum 0.35X	Maximum 2.25X
FOV (½" Horizontal Sensor)	17.6mm	2.8mm
Resolution in Object Space	12 lp/mm	80 lp/mm
Resolution in Image Space	34 lp/mm	35.5 lp/mm
Working Distance (±3mm)	147mm	147mm

Primary Magnification	With 0.5X Lens		With 0.25X Lens	
	Minimum 0.35X	Maximum 2.25X	Minimum 0.175X	Maximum 1.125X
FOV(½" Horizontal Sensor)	17.6mm	2.8mm	35.2mm	5.6mm
Resolution in Object Space	12 lp/mm	80 lp/mm	6 lp/mm	40 lp/mm
Resolution in Image Space	34 lp/mm	35.5 lp/mm	34 lp/mm	35.5 lp/mm
Working Distance (±3mm)	147mm	147mm	275mm	275mm

