





47689INK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 31.744
GD RADIUS : 78.472
SCALE BAR : 200


REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

47689INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 59.0060 μm
DIFFRACTION LIMITED RANGE: 6.285 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

CHROMATIC FOCAL SHIFT



TRANSVERSE RAY FAN PLOT


47689INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 200.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

47689INK
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF



EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM