





+ 0.4861
x 0.5876
■ 0.6563



SURFACE: IM

IM: 0.000 MM

SPOT DIAGRAM

49775INK
TUE DEC 16 2008 UNITS ARE μm.
FIELD :
RMS RADIUS : 5.944
GD RADIUS : 17.076
SCALE BAR : 40


REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

CHROMATIC FOCAL SHIFT

49775INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 76.5625 μm
DIFFRACTION LIMITED RANGE: 21.175 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM




TRANSVERSE RAY FAN PLOT

49775INK
TUE DEC 16 2008
MAXIMUM SCALE: ± 100.000 μm.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



POLYCHROMATIC DIFFRACTION MTF

49775INK
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm.
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM