




CHROMATIC FOCAL SHIFT

SUBJECT: INA

IMP: 0.000 NM

SPOT DIAGRAM

```

497B8INK
TUE DEC 16 2008  UNITS ARE  $\mu$ m.
FIELD          :      1
RMS RADIUS    :      5.944
GED RADIUS    :     17.076
SCALE BAR     :      40


```

REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49788INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 237.9898 μm
DIFFRACTION LIMITED RANGE: 21.175 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)




TRANSVERSE RAY FAN PLOT

49788INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 100.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49788INK
TUE DEC 16 2008
DATA FOR 0.4000 TO 1.0000 μm .
SURFACE: IMAGE



POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)