



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES



49792INK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 50.205
GD RADIUS : 126.496
SCALE BAR : 400

SPOT DIAGRAM


EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

REFERENCE : CHIEF RAY

CHROMATIC FOCAL SHIFT

49792INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 394.6199 μm
DIFFRACTION LIMITED RANGE: 9.445 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM




TRANSVERSE RAY FAN PLOT

49792INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 500.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



POLYCHROMATIC DIFFRACTION MTF

49792INK
TUE DEC 16 2008
DATA FOR 0.4000 TO 1.0000 μm .
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

EO Edmund
optics | worldwide

www.edmundoptics.com