





M4 x 0.7 x 7 DEEP FOR MOUNTING THE KINEMATIC ASSEMBLY (2X)




M3 x 0.2 HEX SOCKET ADJUSTMENT SCREWS (3X)

M3 ADJUSTMENT LOCKING HEX SOCKET SET SCREWS (3X)

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	SM FLAT KINEMATIC MOUNT 2-SCREW	
ALL DIMS IN	mm	DWG NO	34722	SHEET 1 OF 1