





TECHSPEC® ACHROMATIC LENSES



Surface: IMA

Spot Diagram		Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM	
49942 4/24/2017 Units are μm. Field : 1 RMS radius : 1.898 GEO radius : 4.610 Scale bar : 10	Airy Radius: 3.071 μm. Legend items refer to Wavelengths Reference : Chief Ray	49942.ZMX Configuration 1 of 1	

Chromatic Focal Shift		Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM	
49942 4/24/2017 Maximum Focal Shift Range: 63.7870 μm Diffraction Limited Range: 43.128 μm Pupil Zone: 0.0000		49942.ZMX Configuration 1 of 1	



Transverse Ray Fan Plot		Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM	
49942 4/24/2017 Maximum Scale: ± 10.000 μm. 0.486 0.588 0.656 Surface: Image		49942.ZMX Configuration 1 of 1	

Polychromatic Diffraction MTF		Edmund Optics HTTP://WWW.EDMUNDOPTICS.COM	
49942 4/24/2017 Data for 0.4861 to 0.6563 μm. Surface: Image Legend items refer to Field positions		49942.ZMX Configuration 1 of 1	