


NOTES:

- 1. SUBSTRATE:
N-BK7
- 2. COATING (APPLY ACROSS COATING APERTURE)
S1: ALUMINUM COATED W/ PROTECTIVE OVERCOAT
R(AVG)>85% FROM 400-700nm, @ 45° AOI

S2: NONE
3. FINE GRIND SURFACE

- 4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	25.47 x 18	18 x 18
COATING APERTURE	25.47 x 18	18 x 18
SURFACE FLATNESS	$\lambda/4$	$\lambda/4$
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION		Edmund Optics®	
ALL DIMS IN mm		TITLE	20mm, Aluminum Coated, N-BK7 Right Angle Prism
DWG NO		32335	SHEET 1 OF 1