## NOTES:


1. WAVELENGTH RANGE: 400 - 700nm:


2. COATING: UNCOATED


3. FINE GRIND SURFACE

4. ROHS COMPLIANT









SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE ACCURACY	COMMERCIAL POLISH	COMMERCIAL POLISH
SURFACE QUALITY	80-50	80-50
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

	THIRD ANGLE PROJECTION	$\phi \Box$	TIT
_	ALL DIMS IN	mm	DV

	Edmund Optics®	
TITLE	10mm DIA. WHITE DIFFUSING GLASS	
DWG NO	34469 SHEET 1 OF	Γ 1