
NOTES:


- 1. SUBSTRATE MATERIAL: FLOAT GLASS
- 2. ROHS COMPLIANT
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

\$1: 25% R ±5% @ 550nm 75% T ±5% @ 550nm

S2: AR 1/4λ MgF2 @ 550nm







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
SURFACE FLATNESS	4 - 6λ	4 - 6λ
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

				Edmund Optics®		
THIRD ANGLE PROJECTION		TITLE	35 x 35mm, 25 R/75 T, PLATE BEAMSPLITTER			
	ALL DIMS IN	mm	DWG NO	46609	SHEET 1 OF 1	