



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



COMPATIBLE TUBE LENS	Focal Length: 200mm
MAGNIFICATION	2X
MOUNTING THREAD	M26 x 36 TPI
NUMERICAL APERTURE NA	0.055
WORKING DISTANCE (mm)	34
MOUNTING THREADS	M26 x 36 TPI
FOCAL LENGTH FL (mm)	100
TYPE	Plan APO
FIELD OF VIEW, 1" SENSOR	6.4 x 4.8mm
FIELD OF VIEW, 1/2" SENSOR	3.20 x 2.40mm
FIELD OF VIEW, 2/3" SENSOR	4.40 x 3.30mm
FIELD OF VIEW, 24 DIAMETER FIELD EYEPIECE (mm)	12
DEPTH OF FOCUS (μm)	91
RESOLVING POWER (μm)	5
RoHS	NOT COMPLIANT

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® **Edmund Optics**®

THIRD ANGLE PROJECTION

TITLE

2X EO M Plan Apo Long Working Distance  
Infinity Corrected

ALL DIMS IN

mm

DWG NO

59875

SHEET  
1 OF 1