

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING





COMPATIBLE TUBE LENS	Focal Length: 200mm
MAGNIFICATION	50X
MOUNTING THREAD	M26 x 36 TPI
NUMERICAL APERTURE NA	0.42
WORKING DISTANCE (mm)	20.5
MOUNTING THREADS	M26 x 36 TPI
FOCAL LENGTH FL (mm)	4
TYPE	Plan APO ULWD
FIELD OF VIEW, 1" SENSOR	0.256 x 0.192mm
FIELD OF VIEW, 1/2" SENSOR	0.064 x 0.048mm
FIELD OF VIEW, 2/3" SENSOR	0.176 x 0.132mm
FIELD OF VIEW, 24 DIAMETER FIELD EYEPIECE (mm)	0.48
DEPTH OF FOCUS (µm)	1.6
RESOLVING POWER (µm)	0.7
RoHS	NOT COMPLIANT

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

			Edmund Optic	S®
THIRD ANGLE PROJECTION		TITLE	50X EO M Plan Apo ULWD Infinity Corre	ected
ALL DIMS IN	mm	DWG NO	59881	SHEET 1 OF 1