



NOTES:

- 1. SUBSTRATE:
Crystal Quartz and MgF2
- 2. COATING (APPLY ACROSS COATING APERTURE):
S1 & S2: R(AVG) <0.75% @ 450 - 650nm

DAMAGE THRESHOLD,
PULSED: >5 J/cm², 10ns @ 10Hz @ 1064nm
- 3. SURFACE S1 TO BE PARALLEL TO SURFACE S2 TO WITHIN <10 ARCSEC
- 4. RETARDANCE: $\lambda/2 \pm \lambda/100$ @ 20°C
- 5. DESIGN WAVELENGTH: 450 - 650 nm
- 6. TRANSMITTED WAVEFRONT: $<\lambda/4$ @ 632nm
- 7. CONSTRUCTION: Crystalline
- 8. ROHS: COMPLIANT



SECTION A-A

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® **Edmund Optics®**

	S1	S2
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	> Ø34	> Ø34

THIRD ANGLE PROJECTION 		TITLE	50.8mm Dia, 450 - 650nm, $\lambda/2$ Achromatic Waveplate	
ALL DIMS IN	mm	DWG NO	39035	SHEET 1 OF 1