


- NOTES:
- 1. MATERIAL: SCHOTT 24 GLASS WITH EMA
 - 2. CORE/CLAD RATIO: 50/50
 - 3. RoHS: EXEMPT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
DISTORTION (%)	3.00
NUMERICAL APERTURE	1.00
RESOLUTION (lp/mm)	72
RESOLVING POWER	8.00

THIRD ANGLE
PROJECTION

ALL DIMS IN

mm

 Edmund Optics®

TITLE	FIBER OPTIC TAPER FOR 25mm TO 8mm		
DWG NO	55138	SHEET 1 OF 1	