



- NOTES:
- 1. MATERIAL: SCHOTT 24 GLASS WITH EMA
  - 2. CORE/CLAD RATIO: 70/30
  - 3. RoHS: EXEMPT




**FOR INFORMATION ONLY:**  
**DO NOT MANUFACTURE**  
**PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
DISTORTION (%)	3.00
NUMERICAL APERTURE	1.00
RESOLUTION (lp/mm)	102
RESOLVING POWER	6.00

THIRD ANGLE  
PROJECTION



ALL DIMS IN

mm

 Edmund Optics®

TITLE	FIBER OPTIC TAPER FOR 25mm TO 2/3" SENSOR		
DWG NO	55141	SHEET 1 OF 1	