

TECHSPEC® CompactTL™

TELECENTRIC LENSES

#33-115 • f/28.5

TECHSPEC® CompactTL™ Telecentric Lenses are designed for applications with tight space constraints due to their ultra-compact design. These lenses feature a 2/3" sensor format and a variety of different working distance and magnification options. From single unit to high volume implementation, these lenses provide a great price to performance ratio. TECHSPEC® CompactTL™ Telecentric Lenses are perfect for integration into gauging systems due to their excellent telecentricity and low distortion.



Primary Magnification:	2X
Working Distance¹:	300mm
Depth of Field²:	±0.37mm (20% @ 20 lp/mm)
Max. Sensor Format:	2/3"
Camera Mount:	C-Mount
Aperture (f/#):	f/28.5
Distortion %:	<0.029%
Object Space NA:	0.035

Telecentricity:	<0.049°
Type:	Telecentric Lens
Length:	206.26mm
Front Diameter:	31mm
Weight:	129g
RoHS:	Compliant
Number of Elements (Groups):	5 (4)
AR Coating:	MgF ₂ (400-700nm)

1. From front housing 2. Image space MTF contrast

At 300mm W.D.						
Sensor Size	1/4"	1/3"	1/2.5"	1/2"	1/1.8"	2/3"
Field of View³	1.8mm	2.4mm	2.9mm	3.2mm	3.6mm	4.4mm

3. Horizontal FOV on Standard (4:3) sensor format.




Figure 1: Distortion at the maximum sensor format. Positive values correspond to pincushion distortion, negative values correspond to barrel distortion.




Figure 2: Relative illumination (center to corner)

In both plots, field points corresponding to the image circle of common sensor formats are included. Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

MTF & DOF: f/28.5

WD: 300mm

HORIZONTAL FOV: 4.4mm




Figure 3: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are the Tangential and Sagittal values for field points on center, at 70% of full field and the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 4: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.