




NOTES:

1. SUBSTRATE
BOROFLOAT®
2. COATING PERFORMANCE (APPLY ACROSS COATING APERTURE)
T(AVG) <1.0% @ 390 - 570nm
T(AVG) >85% @ 620 - 750nm
T(ABS) <2.0% @ 415 - 550nm
T(ABS) >80% @ 630 - 750nm



3. CUT AND SEAM

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY




	S1	S2					
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION 	TITLE		50 x 50 RED DICHROIC FILTER	
SURFACE QUALITY	80-50	80-50		DWG NO		30634	
CLEAR APERTURE	≥85 %	≥85 %				SHEET 1 OF 1	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm			

NOTES:

1. SUBSTRATE
BOROFLOAT®
2. COATING PERFORMANCE (APPLY ACROSS COATING APERTURE)
T(AVG) >85% @ 390 - 485nm
T(AVG) <1.0% @ 525 - 750nm
T(ABS) >80% @ 400 - 485nm
T(ABS) <1.0% @ 620 - 690nm



△ 3. CUT AND SEAM

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY




	S1	S2				
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION 	TITLE	50 x 50 BLUE DICHROIC FILTER	
SURFACE QUALITY	80-50	80-50		DWG NO	30635	SHEET 1 OF 1
CLEAR APERTURE	≥85 %	≥85 %				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm		

NOTES:

1. SUBSTRATE
BOROFLOAT®
2. COATING PERFORMANCE (APPLY ACROSS COATING APERTURE)
T(AVG) <1.0% @ 400 - 480nm
T(AVG) >80% @ 525 - 555nm
T(AVG) <1.0% @ 590 - 720nm
T(ABS) <1.0% @ 425 - 455nm
T(ABS) >70% @ 530 - 550nm
T(ABS) <1.0% @ 620 - 690nm



3. CUT AND SEAM

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2					
SHAPE	PLANO	PLANO	<div>THIRD ANGLE PROJECTION</div> 	TITLE		50 x 50 GREEN DICHROIC FILTER	
SURFACE QUALITY	80-50	80-50		DWG NO		46139	
CLEAR APERTURE	≥85 %	≥85 %				SHEET 1 OF 1	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm			