

## NOTES:

- 1. SUBSTRATE: VACUUM UV GRADE CaF2
- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO <1 arcmin
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AVG) < 1% FROM 1650-3000nm @ 0° AOI R(ABS) < 2% FROM 1650-3000nm @ 0° AOI







## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE QUALITY	40-20	40-20	
CLEAR APERTURE	Ø27.00	Ø27.00	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	

			<b>G</b>	Edmund Option	;S®
	THIRD ANGLE _ PROJECTION	$\phi \lhd$	TITLE	Ø30mm, BBAR(1650 - 3000nm), CALCIUM FLUORIDE WINDOW	
)	ALL DIMS IN	mm	DWG NO	15969	SHEE 1 OF