





NOTES:

1. SUBSTRATE: Hoya UV30N



LONGPASS FILTER

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
Δλ	<40
TH (%)	>85
CUT-ON WAVELENGTH (nm)	300±7
SURFACE QUALITY	60-40
WAVELENGTH	UV
BEVEL	PROTECTIVE AS NEEDED

 **Edmund Optics®**



ALL DIMS IN

mm

TITLE

Hoya UV30N (300nm), 12.5mm Dia., 2.5mm
Thick, Colored Glass Longpass Filter

DWG NO

18800

SHEET
1 OF 1