





NOTES:

- SUBSTRATE: Hoya RM100



LONGPASS FILTER



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
$\Delta\lambda$	N/A
TH (%)	N/A
CUT-ON WAVELENGTH (nm)	1000
SURFACE QUALITY	60-40
WAVELENGTH	IR
BEVEL	PROTECTIVE AS NEEDED



ALL DIMS IN

mm



**Edmund Optics®**

TITLE

Hoya RM100 (1000nm), 50.8mm Sq., 2.5mm  
Thick, Colored Glass Longpass Filter

DWG NO

18918

SHEET  
1 OF 1