

[See all 76 Products in Family](#)

# LightPath 354064 | 6mm Dia., 0.24 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#37-111** **20+ In Stock**

⊖ 1 ⊕ **A\$120<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-10	<b>A\$120.00</b> each
Qty 11-49	<b>A\$108.00</b> each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

Thickness: 0.25 (t) (mm)  
Material: BK7

**Compatible Window:**

354064

**Lightpath Lens Code:**

Aspheric Lens

**Type:**

Collimate or Focus Laser Light

**Typical Applications:**

## Physical & Mechanical Properties

6.00 ±0.015 Diameter (mm):

5.2 Clear Aperture CA (mm):

2.59 Edge Thickness ET (mm):

3.10 ±0.05 Center Thickness CT (mm):

Protective as needed Bevel:

8.706 Distance from Window to Lens (D) (mm):

## Optical Properties

11.00 @ 633nm Effective Focal Length EFL (mm):

0.24 Numerical Aperture NA:

D-ZK3 Substrate: □

±1 Focal Length Tolerance (%):

633 Aspheric Design Wavelength (nm):

BBAR (1050-1600nm) Coating:

R<sub>abs</sub> <1.0% @ 1050 - 1600nm Coating Specification:

80-50 Surface Quality:

2.50 f#:

50.22 Abbe Number (v<sub>d</sub>):

1.586 Index of Refraction (n<sub>d</sub>):

1050 - 1600 Wavelength Range (nm):

9.3 Working Distance (mm):

Infinite Conjugate Distance:

633.00 Focal Length Specification Wavelength (nm):

< 0.09 Transmitted Wavefront Error (λ, RMS):

## Material Properties

7.6 Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):

## Environmental & Durability Factors

≤200 Operating Temperature (°C):

## Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 247:

## Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.

## Technical Information



## Compatible Mounts