

[See all 77 Products in Family](#)

# LightPath 355110 | 7.2mm Dia., 0.40 NA, BBAR (1050-1600nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#87-127** [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕ **A\$142<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-10	<b>A\$142.40</b> each
Qty 11-49	<b>A\$128.00</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Thickness: 0.28 (t) (mm)  
Material: BK7

**Compatible Window:**

355110

**Lightpath Lens Code:**

Aspheric Lens

**Type:**

Collimate or Focus Laser Light

Typical Applications:

## Physical & Mechanical Properties

7.20 ±0.020 Diameter (mm):

5 Clear Aperture CA (mm):

4.25 Edge Thickness ET (mm):

5.16 ±0.05 Center Thickness CT (mm):

Protective as needed Bevel:

2.682 Distance from Window to Lens (D) (mm):

## Optical Properties

6.24 @ 780nm Effective Focal Length EFL (mm):

0.40 Numerical Aperture NA:

[D-ZLaF52LA](#) Substrate: □

±1 Focal Length Tolerance (%):

780 Aspheric Design Wavelength (nm):

BBAR (1050-1600nm) Coating:

R<sub>abs</sub> <1.0% @ 1050 - 1600nm Coating Specification:

40-20 Surface Quality:

1.25 f#:

40.79 Abbe Number (v<sub>d</sub>):

1.806 Index of Refraction (n<sub>d</sub>):

1050 - 1600 Wavelength Range (nm):

3.5 Working Distance (mm):

Infinite Conjugate Distance:

780.00 Focal Length Specification Wavelength (nm):

< 0.07 Transmitted Wavefront Error (λ, RMS):

## Material Properties

6.9 Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):

## Environmental & Durability Factors

≤200 Operating Temperature (°C):

## Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 247:

## Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser



## Technical Information

