

[See all 36 Products in Family](#)

# 0.9 OD 75 x 75mm Neutral Density Filter



Stock **#54-458** **8 In Stock**

-

1

+

A\$403<sup>.20</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | A\$403.20 each                |
| Qty 11-49      | A\$337.60 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Neutral Density Filter

Physical & Mechanical Properties

|                   |  |                  |
|-------------------|--|------------------|
| 75 x 75 (Nominal) |  | Dimensions (mm): |
| 75.00             |  | Length (mm):     |
| 75.00             |  | Width (mm):      |

| Optical Properties |                                     |
|--------------------|-------------------------------------|
| 0.9                | Optical Density OD (Average):       |
| Wratten 2          | Substrate: <input type="checkbox"/> |
| Uncoated           | Coating:                            |
| 13.00              | Transmission (%):                   |
| 400 - 700          | Blocking Wavelength Range (nm):     |

| Regulatory Compliance |                             |
|-----------------------|-----------------------------|
| Compliant             | RoHS 2015:                  |
| Compliant             | Reach 223:                  |
| View                  | Certificate of Conformance: |

## Product Details


Storage in humid environments can cause the filters to cloud and temperatures should not exceed 50°C for extended periods. Every 0.3 density increment equals one f-stop.

- Available in Large Sizes
- Easily Cut for Custom Sizing
- Kodak Filter No. 96

Kodak Wratten 2 Neutral Density Filters are used in image forming optical systems to reduce light intensity across the visible spectrum without altering the spectral profile. These ND filters feature tolerances of ±10% of the nominal diffuse density. Although the filters transmit the infrared spectrum, neutrality is controlled only in the visible spectrum. Kodak Wratten 2 Neutral Density Filters are uncoated and have a blocking wavelength range of 400-700nm. All ND filters are 0.1mm in thickness and can be cut for easy custom sizing.

**Note:** Storage in humid environments can cause the filters to cloud and temperatures should not exceed 50°C for extended periods. Every 0.3 density increment equals one f-stop.

## Technical Information



## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools