

[See all 41 Products in Family](#)

TECHSPEC® 1025nm 12.5mm Diameter, OD 2.0 Shortpass Filter



TECHSPEC OD 2.0 Shortpass Filters

Stock **#64-644** **1 In Stock**

⊖ 1 ⊕ **A\$156⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-5	A\$156.80 each
Qty 6-25	A\$140.80 each
Qty 26-49	A\$134.40 each
Need More?	Request Quote

Product Downloads

General

Shortpass Filter **Type:**

Physical & Mechanical Properties

12.50 +0.0/-0.2 **Diameter (mm):**

1.50 ±0.1 **Thickness (mm):**

80.00 Clear Aperture (%):

Optical Properties

0 Angle of Incidence (°):

≥2.0 Optical Density OD (Average):

1,025.00 Cut-Off Wavelength (nm):

[Fused Silica](#) (Coming 7980) Substrate:

Traditional Coated Coating:

1110 - 1340 Rejection Wavelength (nm):

40-20 Surface Quality:

>85 Transmission (%):

475 - 975 Transmission Wavelength (nm):

λ/4 Transmitted Wavefront, P-V:

±3 Slope Factor (%):

±2 Cut-Off Tolerance (%):

475 - 1340 Wavelength Range (nm):

Regulatory Compliance

[Compliant](#) RoHS 2015:

[Compliant](#) Reach 224:

[View](#) Certificate of Conformance:




Product Details

- Sharp Cut-Off Wavelength
- High Transmission / Rejection Efficiency
- Precision Fused Silica Substrate

Our TECHSPEC® OD 2.0 Shortpass Filters are designed to have a very sharp transition from transmission to reflection, making them extremely useful in several applications. With an average transmission of 85% and an average blocking optical density of 2.0, excellent contrast can be achieved in machine vision and gauging applications. Available in a variety of cut-off wavelengths, they are ideal for fluorescence applications, separating spectral orders, and creating custom, efficient bandpass filters when combined with [TECHSPEC® OD 2.0 Longpass Filters](#). TECHSPEC® OD 2.0 Shortpass Filters have a single layer of AR coating on the back surface that enhances the overall efficiency of each filter. These filters are designed with a precision fused silica substrate.

Note: Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact kits@edmundoptics.com.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts