

[See all 102 Products in Family](#)

10.5mm Diameter x 9.45mm FL, MgF₂ Coated, Aspheric Condenser Lens



Stock #15-530 **1 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ A\$101⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$101.60 each
Qty 11-49	A\$91.20 each
Need More?	Request Quote

Product Downloads

General

Condenser Lens **Type:**

Physical & Mechanical Properties

10.50 +0.00/-0.15 **Diameter (mm):**

≤30 **Centering (arcmin):**

Clear Aperture CA (mm):

9.8

Edge Thickness ET (mm):

1.1

Center Thickness CT (mm):

3.80 ±0.2

Bevel:

Protective as needed

Diameter of Asphere (mm):

10.5

Shape of Back Surface:

Plano

Optical Properties

Effective Focal Length EFL (mm):

9.45

Numerical Aperture NA:

0.56

Back Focal Length BFL (mm):

8.10

Substrate: □

[N-F2](#)

Focal Length Tolerance (%):

±7

Coating:

MgF₂ (400-700nm)

Coating Specification:

R_{avg} ≤ 1.75% @ 400 - 700nm

Surface Quality:

80-50 (typical)

f/#:

0.9

Abbe Number (v_d):

36.43

Index of Refraction (n_d):

1.620

Radius R₂ (mm):

Plano

Wavelength Range (nm):

400 - 700

Conjugate Distance:

Infinite

Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

7.8

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 235:


[Compliant](#)

Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

Technical Information





Coating Curves