

12.7mm Beam Steering Assembly



12.7mm Beam Steering Assembly, #67-362

Stock **#67-362** 1 In Stock

-

1

+

A\$633⁶⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$633.60 each
Qty 11+	A\$602.72 each
Need More?	Request Quote

Product Downloads

General

Adjustable - Beam Steering	Type:
Circular	Type of Optics:
360° Horizontal, 6° Tilt	Range:

Physical & Mechanical Properties

Construction:

Black Anodized Aluminum & Stainless Steel

Post Diameter (mm):

12.7

12.7 Post Diameter (mm):

Threading & Mounting

25.0 - 25.4	Size of Compatible Optics (mm):
-------------	---------------------------------

25.0 - 25.4

Regulatory Compliance	
GDPR	Compliant
SOX	Compliant
HIPAA	Compliant
PCI DSS	Compliant
ISO 27001	Compliant
Other	Compliant

[View](#) **Certificate of Conformance:**

Product Details

- Ready to Use Beam Steering Assembly
- High Resolution 100 TPI Kinematic Mounts
- Available with 20mm Post for Higher Stability

Beam Steering Assemblies are specifically suited for numerous applications in laser holography, interferometry and other exacting set-ups and systems requiring precise redirection of an optical beam. The 12.7mm Beam Steering Assembly comprises a slotted base, suitable for attachment to metric and imperial bench plates, a main 300mm post and two 100 TPI kinematic mounts with 6° tilt range, suitable for 1" or 25mm diameter optics. The kinematic mounts can be moved vertically and can also be rotated 360° around the main post. The 20mm Beam Steering Assembly is designed for applications that require a higher level of stability and feature a larger slotted base than its 12.7mm counterpart; it includes a 20mm main post and heavy duty cross clamps. Mirrors are held in place with an #8 set screw.

Technical Information

