

12.7mm Dia, 340 - 560nm, $\lambda/4$ Achromatic Waveplate



Achromatic Waveplates (Retarders)

Stock **#39-024** **3 In Stock**

-

1

+

A\$1,440⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$1,440.00 each
Qty 6+	A\$1,176.00 each
Need More?	Request Quote

Product Downloads

General	
Achromatic Waveplate	Type:
Air Spaced	Configuration:
Physical & Mechanical Properties	
>8.0	Clear Aperture CA (mm):
	Diameter (mm):

12.70	
	Thickness (mm):
6.00 ±0.2	
	Dimensional Tolerance (mm):
+0/-0.25	
	Construction:
Crystalline	
	Parallelism (arcsec):
<10	
	Housing Tolerance (mm):
+0/-0.25	

Optical Properties

	Coating:
R _{avg} <0.75% @ 340 - 560nm	
	Substrate: □
Crystal Quartz and MgF ₂	
	Retardance:
$\lambda/4$	
	Surface Quality:
40-20	
	Transmitted Wavefront, P-V:
< $\lambda/4$ @ 632nm	
	Retardance Tolerance:
$\lambda/100$ @ 20°C	
	Coating Specification:
R _{avg} <0.75% @ 340 - 560nm	
	Wavelength Range (nm):
340 - 560	
	Damage Threshold, By Design: □
>5 J/cm ² @ 1064nm, 10ns, 10Hz	

Regulatory Compliance

	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 247:
Compliant	


Product Details

- Multiple Wavelength Ranges Available
- Flat Response Over Each Broad Spectral Range
- $\lambda/4$ and $\lambda/2$ Retardance
- Mounted in Black Anodized Aluminum Housing






Achromatic Waveplates (Retarders) provide a constant phase shift independent of the wavelength of light that is used. This wavelength independence is achieved by using two different birefringent crystalline materials. The relative shifts in retardation over the wavelength range are balanced between the two materials used. Achromatic Waveplates (Retarders), with their flat response, are ideal for use with tunable lasers, multiple laser line systems, and other broad-spectrum sources.

Designed to be used at an angle of incidence of 0°, changes of ±3° will yield less than 1% change in retardance. The 23mm clear aperture waveplates will feature a cemented construction. All Achromatic Waveplates (Retarders) are mounted in an anodized aluminum housing with the fast axis clearly indicated.

Technical Information



25.4mm Diameter Waveplates



30.0mm Diameter Waveplates

