

**TECHSPEC® 12.7mm Dia., 532 & 1064nm T, 355nm R 45° Thin Harmonic Separator**



TECHSPEC Nd:YAG Harmonic Separators

Stock #29-044 **14 In Stock**

⊖ 1 ⊕ A\$361<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	A\$361.60 each
Qty 6-24	A\$324.80 each
Qty 25-49	A\$289.60 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Window Substrate **Type:**

**Physical & Mechanical Properties**

90 **Clear Aperture (%):**

Dichroic **Construction:**

12.70 +0.00/-0.10 **Diameter (mm):**

<3 **Parallelism (arcmin):**

3.18 ± 0.20 **Thickness (mm):**

## Optical Properties

45 **Angle of Incidence (°):**

**Coating Specification:**  
Surface 1: R<sub>abs</sub>: >99% @ 355nm, T<sub>abs</sub>: >95% @ 532, 1064nm  
Surface 2: R<sub>abs</sub>: <0.75% @ 532, 1064nm

355 **Reflection Wavelength (nm):**

**Substrate:**   
[Fused Silica](#) (Corning 7980)

λ/10 **Surface Flatness (P-V):**

10-5 **Surface Quality:**

532, 1064 **Transmission Wavelength (nm):**

**Damage Threshold, By Design:**   
Surface 1:  
2.5 J/cm<sup>2</sup> @ 355nm, 20ns, 20Hz  
5 J/cm<sup>2</sup> @ 532nm, 20ns, 20Hz  
7.5 J/cm<sup>2</sup> @ 1064nm, 20ns, 20Hz  
Surface 2:  
15 J/cm<sup>2</sup> @ 1064nm, 20ns, 20Hz  
10 J/cm<sup>2</sup> @ 532nm, 20ns, 20Hz

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Used to Separate Nd:YAG Harmonic Wavelengths
- Beamsplitter Coating Features >95% Transmission
- λ/10 Fused Silica Substrate

TECHSPEC® Nd:YAG Harmonic Separators are used to separate the common harmonic wavelengths of an Nd:YAG laser. A beamsplitter coating on the first surface reflects at least one wavelength and transmits another. The second surface of the beamsplitter features an anti-reflective coating to minimize the loss due to reflection. TECHSPEC Nd:YAG Harmonic Separators are available in 45° and 0° angle of incidence options. These harmonic separators are available in multiple wavelength configurations for optimal flexibility in system design.

**Note:** The Damage Threshold values we publish for this family of products were all tested independently from one another. When using these products with more than 1 incident beam, the resulting Damage Threshold of the system will be negatively impacted.