

TECHSPEC[®] 12.7mm Dia. x 25.4mm FL, 3-12μm BBAR Coated, ZnSe Plano-Convex Lens

See More by [Coherent®](#)



TECHSPEC Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

Stock **#11-420** **6 In Stock**

[Other Coating Options](#)

-

1

+

A\$718⁻⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$718.40 each
Qty 11-25	A\$646.40 each
Qty 26-49	A\$507.20 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

12.70 +0.00/-0.10

Diameter (mm):

≤50.8	Centering, ETD (μm):
2.50 ±0.10	Center Thickness CT (mm):
1.93	Edge Thickness ET (mm):
11.43	Clear Aperture CA (mm):
Protective as needed	Bevel:

<50 RMS	Surface Roughness (□):
---------	------------------------

Optical Properties

25.40 @ 10.6μm	Effective Focal Length EFL (mm):
24.36	Back Focal Length BFL (mm):

BBAR (3000-12000nm)	Coating:
Ravg ≤3.0% @ 3 - 12μm	Coating Specification:

Coherent® Infrared ZnSe	Substrate: □
40-20	Surface Quality:

λ	Power (P-V) @ 632.8nm:
λ/20	Irregularity (P-V) @ 10.6μm:

35.63	Radius R ₁ (mm):
2.00	f/#:

0.25	Numerical Aperture NA:
3000 - 12000	Wavelength Range (nm):

<0.0005 @ 10.6μm	Bulk Absorption Coefficient (cm ⁻¹):
------------------	--

Electrical

λ/10	Power (P-V) @ 10.6μm:
------	-----------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Compliant	Reach 242:
-----------	------------

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Edmund Optics® Designed, Coherent® Manufactured
- Premier Grade ZnSe Material
- Uncoated or Broadband AR Coating Options

TECHSPEC® Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses are designed for focusing or collimation applications in the mid-wave and longwave infrared spectrum. Manufactured by Coherent®, these lenses feature Infrared ZnSe material with <0.0005cm⁻¹ bulk absorption at 10.6μm and are available uncoated or with a variety of broadband anti-reflection coating options. The 8-12μm coating is ideal for use with CO₂ lasers and thermal camera applications, whereas the dual band 3-12μm coating is ideal for hyperspectral applications. TECHSPEC® Zinc Selenide PCX Lenses feature an irregularity of <λ/20 at 10.6μm, 40-20 surface quality, and <50Å surface roughness. Three diameter options are available, with effective focal lengths ranging from 12.7mm to 250mm.

Notes: II-VI Incorporated is now Coherent Corp.

Special care should be taken when handling Zinc Selenide as it is a toxic material. Always wear rubber or plastic gloves to avoid risk of contamination.

Technical Information



AR COATED ZINC SELENIDE																					
ZnSe with 3-12μm AR Coating Typical Transmission <table><caption>Approximate data for ZnSe with 3-12μm AR Coating</caption><tr><th>λ (μm)</th><th>T (%)</th></tr><tr><td>2.5</td><td>70</td></tr><tr><td>3</td><td>95</td></tr><tr><td>4</td><td>97</td></tr><tr><td>5</td><td>95</td></tr><tr><td>6</td><td>96</td></tr><tr><td>8</td><td>95</td></tr><tr><td>10</td><td>96</td></tr><tr><td>12</td><td>94</td></tr><tr><td>14</td><td>86</td></tr></table> Typical transmission of a ZnSe window with BBAR (3000-12000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} < 5.0\% @ 3 - 12\mu m$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data	λ (μm)	T (%)	2.5	70	3	95	4	97	5	95	6	96	8	95	10	96	12	94	14	86	
λ (μm)	T (%)																				
2.5	70																				
3	95																				
4	97																				
5	95																				
6	96																				
8	95																				
10	96																				
12	94																				
14	86																				
ZnSe with 8-12μm AR Coating Typical Transmission <table><caption>Approximate data for ZnSe with 8-12μm AR Coating</caption><tr><th>λ (μm)</th><th>T (%)</th></tr><tr><td>6</td><td>70</td></tr><tr><td>7</td><td>90</td></tr><tr><td>8</td><td>99</td></tr><tr><td>9</td><td>99</td></tr><tr><td>10</td><td>99</td></tr><tr><td>11</td><td>99</td></tr><tr><td>12</td><td>97</td></tr><tr><td>14</td><td>86</td></tr></table> Typical transmission of a ZnSe window with BBAR (8000-12000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 8 - 12\mu m$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data	λ (μm)	T (%)	6	70	7	90	8	99	9	99	10	99	11	99	12	97	14	86			
λ (μm)	T (%)																				
6	70																				
7	90																				
8	99																				
9	99																				
10	99																				
11	99																				
12	97																				
14	86																				

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Compatible Mounts

;