

12mm Focal Length, Prism Optimized Fixed Focal Length Lens



12mm Focal Length, Prism Optimized Fixed Focal Length Lens

Stock **#90-619** NEW **1 In Stock**

-

1

+

A\$2,072⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$2,072.00 each
Need More?	Request Quote

Product Downloads

General

Series:

Prism Optimized Fixed Focal Length Imaging Lenses

Model Number:

JVS-C118-1218-C3

Imaging Lens Type:

Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:

Manual Iris

56.00	Length (mm):
32.00	Maximum Diameter (mm):
4.00	Maximum Rear Protrusion (mm):
Optical Properties	
9.00	Maximum Image Circle (mm):
-0.80	TV Distortion (%):
12.00	Focal Length FL (mm):
150 - ∞	Working Distance (mm):
1.8	Aperture (f/#):
VIS-NIR	Wavelength:
Sensor	
1/1.8"	Maximum Sensor Format:
3.45 x 3.45	Pixel Size, H x V (µm):
Threading & Mounting	
M27.0 x 0.5	Filter Thread:
C-Mount	Mount:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Designed for use with Multi Sensor Cameras
- Available with Focal Lengths of 6, 8, 12, and 16mm
- C-Mount Compatible with Low Distortion over a Broad Working Distance Range

Prism Optimized Fixed Focal Length Imaging Lenses are designed to utilize the full benefits of prism technology by compensating for the different optical paths and focusing characteristics of multi-sensor cameras. These cameras separate incoming light into multiple channels, with pixel-precise alignment regardless of motion or viewing angle. By directing specific wavelengths to optimized sensors, prism-optimized lenses deliver sharper, higher-quality images with better color fidelity than standard imaging lenses. Prism Optimized Fixed Focal Length Imaging Lenses are designed to be used with multi-sensor cameras such as the [JAI Apex Series](#) or the [JAI Fusion Series](#). These lenses are ideal for applications requiring exceptional color accuracy, precise spatial resolution, and simultaneous imaging across multiple spectral bands.