

[See all 67 Products in Family](#)

LightPath 355110 | 1550nm Alignment, 0.40 NA Fiber Collimator w/ SMA Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock #83-731 **20+ In Stock**

⊖ 1 ⊕ A\$371²⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$371.20 each
Qty 11-25	A\$328.00 each
Qty 26-49	A\$308.80 each
Need More?	Request Quote

Product Downloads

General

355110 **Lightpath Lens Code:**
Fiber Collimator **Type:**

Lens Included:

#87-127

Physical & Mechanical Properties

5.00 Clear Aperture CA (mm):

Protective as needed

Bevel:

Construction:

304L Stainless Steel Housing

11.00 Housing Diameter (mm):

13.00 Housing Length (mm):

Optical Properties

6.24 @ 780nm Effective Focal Length EFL (mm):

0.40 Numerical Aperture NA:

Substrate:

D-ZLaF52LA

Coating:

BBAR (1050-1600nm)

Coating Specification:

R_{abs} <1.0% @ 1050 - 1600nm

Surface Quality:

40-20

f#:

1.25

Abbe Number (v_d):

40.99

Index of Refraction (n_d):

1.806

Wavelength Range (nm):

1050 - 1600

Conjugate Distance:

Infinite

Focal Length Specification Wavelength (nm):

780

Alignment Wavelength (nm):

1550

Transmitted Wavefront Error (λ, RMS):

<0.070

Hardware & Interface Connectivity

Connector:

SMA

Threading & Mounting

Mount:

M11 x0.5

Material Properties

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

6.9

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

Reach 247:

Compliant

Product Details

- Easy to Integrate
- Models for FC/PC, FC/APC, and SMA Connections Available
- Four Wavelength Ranges Covering 350-1600nm

LightPath® Fiber Optic Collimators are designed to collimate light exiting a fiber to a desired beam diameter or spot size or to focus light into a fiber when used in reverse. The lenses are diffraction limited, so they can achieve spot sizes down to a few microns. Lenses also feature an antireflection coating for low back reflection. LightPath® Fiber Optic Collimators are designed so that they can be used in pairs to couple the input and output light of optical devices. Optimum performance for long-term use is ensured by the factory set and tested lens alignment. Typical applications can include use with fiber coupled lasers and pigtailed receptacles, as well as communications and data transfer.

Technical Information

