

[See all 8 Products in Family](#)

**TECHSPEC® 15mm VIS 0°, N-BK7 Right Angle Prism (Hypotenuse Coated)**



Broadband Anti-Reflection Coated Hypotenuse Prism

Stock **#34-403** **6 In Stock**

⊖ 1 ⊕ **A\$204<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>A\$204.80</b> each
Qty 6-25	<b>A\$163.20</b> each
Qty 26-49	<b>A\$154.40</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Right Angle Prism **Type:**

**Physical & Mechanical Properties**

**Dimensional Tolerance (mm):**  
+0/-0.1

**Bevel:**  
Protective as needed

21.20 Length of Hypotenuse (mm):

15.00 Length of Legs (mm):

## Optical Properties

±15 Beam Deviation (arcsec):

VIS 0° (425-675nm) Coating:

N-BK7 Substrate: □

40-20 Surface Quality:

Left-Handed Image Orientation:

$R_{avg} \leq 0.4\%$  @ 425 - 675nm Coating Specification:

90 Ray Deviation (°):

350 - 2200 Wavelength Range (nm):

1.25 Power (fringes) @ 632.8nm:

0.25 Irregularity (fringes) @ 632.8nm:

## Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 235:

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Single Axis Retroreflector
- Right-Handed Image
- VIS and NIR Options Available

TECHSPEC® Broadband Anti-Reflection (BBAR) Coated N-BK7 Right Angle Prisms (Hypotenuse Coated) are ideal for applications that require a single axis retroreflector. These prisms feature coating options that cover the visible and near-infrared spectrum, as well as tight angular tolerances. These TECHSPEC® Broadband Anti-Reflection (BBAR) Coated N-BK7 Right Angle Prisms (Hypotenuse Coated) are also available in custom sizes.

## Technical Information





*Right Angle Prism Ray Path*



*Right Angle Prism Ray Path*



*Right Angle Prism Tunnel Diagram*



*Right Angle Prism Tunnel Diagram*

## Coating Curves

---