


2 μm Aperture Diameter, 1" OD Mounted, Precision Pinhole



Stock #90-288 **NEW** 2 In Stock

1 **A\$262^{.40}**

ADD TO CART



Volume Pricing	
Qty 1-5	A\$262.40 each
Qty 6+	A\$233.60 each
Need More?	Request Quote

General

Type: Mounted

Physical & Mechanical Properties

Outer Diameter (mm): 25.4
+0.000/-0.05

Construction: Stainless Steel

Fixed Aperture Diameter (μm): 2

Thickness (mm): 0.01 Nominal

Aperture Tolerance (μm): ±0.5

Aperture Centration (μm): ±125

Threading & Mounting

Mount Thickness (mm): 2.54

Regulatory Compliance

RoHS 2015: **Compliant**

Certificate of Conformance: [View](#)

Reach 247: **Compliant**

Product Details

- Available in Aperture Mounts for a Secure Mechanical Support
- Pinhole Sized Ranging from 1 to 1,000 Microns
- **High Power Apertures** Available

Unmounted Precision Pinholes

Precision Pinholes are high quality apertures centered to ±0.002" (50 microns). They are constructed of stainless steel and are 3/8" (9.5mm) in diameter. Smaller diameter pinholes will reduce energy throughput, while larger diameter pinholes will pass more spatial noise. Precision pinholes have sizes ranging from 1 to 1,000 microns. Typical applications include leak detection, aerosol studies, holography, fiber optics guides, spatial filtering, research, and more.

Use the [Precision Pinhole Mount](#) to integrate unmounted pinholes into a variety of mechanical components easily.

Mounted Precision Pinholes

Precision Pinholes are available in aperture mounts for secure mechanical support. The mounts also fit into various optical assemblies. Each 9.5mm diameter pinhole is sealed within a 25mm diameter black-anodized aluminum mount. The mount is clearly labeled with a pinhole aperture diameter for easy identification.

Note: Aperture Centering to Mount ± 125 microns.

Edmund Optics offers a wide selection of precision pinholes for leak detection, aerosol studies, holography, fiber optic guides, spatial filtering, research, and more. These pinholes are available in a range of diameters and are ideal for controlling light propagation. Each pinhole is manufactured using high-accuracy techniques, providing consistent circular aperture geometry and high edge quality. Available in both mounted and unmounted formats, these pinholes support a variety of optical setups, from experimental labs to industrial environments.

Technical Information

Related Products



Precision Pinhole Mount



Compact Mirror & Lens Mounts

Frequently Purchased Together



#55-530 - 10.0 - 60.0mm
Optic Height, Metric Bar-Type
Optic Holder
A\$172.80

Qty



#56-274 - 5µm Aperture Diameter,
Mounted, Precision Pinhole
A\$157.60

Qty



#58-514 - 50mm Square Metric
Magnetic Base
A\$192.00

Qty



#58-973 - 76.2mm Length, M6
Thread, Post Holder
A\$25.20

Qty



Resources

Media Type

- FAQ
- Glossary
- Application Note
- Trending in Optics
- Video

? FAQ

What do
spatial filters
do and how do
I use them?

GLOSSARY

Spatial Filter

APPLICATION NOTE

Understanding
Spatial Filters

? FAQ

? FAQ

GLOSSARY

Do you have
any
components
that would...

Do your iris
diaphragms
have
mounts for...

Axial Runout

[View More](#)