

TECHSPEC[®] 20mm Uncoated, Fused Silica Penta Prism



Stock #49-018 CLEARANCE 20+ In Stock

-

1

+

A\$209^{.60}

ADD TO CART

Volume Pricing	
Qty 1+	A\$209.60 each
Need More?	Request Quote

Product Downloads

General

Type:

Penta Prism

Physical & Mechanical Properties

Dimensional Tolerance (mm):

±0.10

Bevel:

Protective as needed

Optical Properties

Coating:

Uncoated	
	Substrate: ☐
Fused Silica (Corning 7980)	
Surface Quality:	
20-10	
Angle Tolerance (arcmin):	
±1	
Image Orientation:	
Right-Handed	
Ray Deviation (°):	
90	
Wavelength Range (nm):	
200 - 2200	
Power (fringes) @ 632.8nm:	
0.20	
Irregularity (fringes) @ 632.8nm:	
0.20	



Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details

- Ray Deviation of 90°
- Right Handed Image
- Optical Tool for Defining a Right Angle
- Additional [Penta Prism](#) Options Available


Penta prisms are five-sided prisms featuring a ray deviation of 90° and a right handed image. The UV-AR coated options also have aluminized reflecting surfaces for increased efficiency. Slight movement of the prism does not affect the true right angle at which light rays are reflected, making a penta prism the ideal optical tool for defining a right angle in an optical system. TECHSPEC® UV Fused Silica Penta Prisms are made from UV fused silica which features low thermal expansion and excellent transmission throughout the UV, VIS, and NIR spectral ranges.

Technical Information



>

Stock No.	A	B
#49-016	5.00mm	6.10mm
#49-020		
#49-017	10.00mm	11.95mm
#49-021		
#49-018	20.00mm	21.65mm
#49-022		
#49-019	25.00mm	27.90mm
#49-023		



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).