

[See all 2 Products in Family](#)

25.4mm Dia. x 152.4mm FL, Uncoated, ISP Optics Barium Fluoride (BaF₂) DCX Lens | BF-BX-25-150

See More by [ISP Optics](#)



Stock **#24-740** **CLEARANCE** **1 In Stock**

-

1

+

A\$708^{.80}

ADD TO CART

Volume Pricing	
Qty 1-9	A\$708.80 each
Qty 10+	A\$638.40 each
Need More?	Request Quote

Product Downloads

General	
Double-Convex Lens	Type:
BF-BX-25-150	Model Number:

Physical & Mechanical Properties	
25.40 +0.00/-0.13	Diameter (mm):
<3	Centering (arcmin):
Protective as needed	Bevel:
3.20 ±0.20	Center Thickness CT (mm):
2.00	Edge Thickness ET (mm):
22.86	Clear Aperture CA (mm):
Optical Properties	

150.00 @ 5µm	Effective Focal Length EFL (mm):
Uncoated	Coating:
Barium Fluoride (BaF ₂)	Substrate: □
60-40	Surface Quality:
λ	Irregularity (P-V) @ 632.8nm:
134.90	Radius R ₁ (mm):
134.9	Radius R ₂ (mm):
5.91	f/#:
±2	Focal Length Tolerance (%):
0.08	Numerical Aperture NA:
200 - 12000	Wavelength Range (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Excellent Transmission from 0.2 - 12µm
- Provide High Transmission without AR Coatings
- Ideal for Infrared Spectroscopy and Infrared Imaging Applications

ISP Optics Barium Fluoride (BaF₂) Double-Convex (DCX) Lenses are ideal for infrared spectroscopy and infrared imaging applications requiring high transmission from 0.2 – 12µm. Barium Fluoride features a low index of refraction, enabling excellent transmission from the Vacuum-UV (VUV) to the Long-Wave Infrared (LWR) without the need for Anti-Reflection (AR) coatings. These lenses also provide higher resistance to high-energy radiation than Calcium Fluoride, even though they have similar physical properties. ISP Optics Barium Fluoride (BaF₂) Double-Convex (DCX) Lenses can be used up to 800°C in a dry environment, but prolonged exposure to moisture can degrade transmission in the ultraviolet range.

Note: These lenses are very sensitive to thermal shock.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools