

TECHSPEC® 25.4mm Dia. x 6.35mm 532/630-655/1064nm, Dual Band Laser Mirror



Stock #26-927 **20+ In Stock**

⊖ 1 ⊕ A\$321^{.00}

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-5 | A\$321.60 each |
| Qty 6-25 | A\$305.60 each |
| Qty 26-49 | A\$292.80 each |
| Need More? | Request Quote |

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

<3 **Parallelism (arcmin):**

>90 **Clear Aperture (%):**

| | |
|---|--|
| Commercial Polish | Back Surface: |
| 25.40 +0/-0.1 | Diameter (mm): |
| 6.35 ±0.10 | Thickness (mm): |
| Optical Properties | |
| 10-5 | Surface Quality: |
| 99.5 | Reflection at DWL (%): |
| Coating Specification: R _{avg} ≥99.50% @ 532nm & 1064nm @ 45° AOI R _{avg} ≥80% @ 630 – 655nm @ 45° AOI | |
| λ/10 | Surface Flatness (P-V): |
| Dielectric | Coating Type: |
| Laser Mirror (532, 635, 650, 1064nm) | Coating: |
| 532, 635, 650, 1064 | Design Wavelength DWL (nm): |
| 45 | Angle of Incidence (°): |
| Fused Silica (Coming 7980) | Substrate: <input type="checkbox"/> |
| Not Specified | Damage Threshold, Reference: <input type="checkbox"/> |

| | |
|------------------------------|------------------------------------|
| Regulatory Compliance | |
| View | Certificate of Conformance: |

Product Details

- >99% Reflectivity at Design Wavelengths
- 10-5 Surface Quality for Sensitive Laser Applications
- 532/1064nm, 635-670/1064nm, or 800/1030nm Wavelength Bands
- [TECHSPEC® Nd:YAG Laser Line Mirrors](#) Also Available

TECHSPEC® Dual Band Laser Line Mirrors feature high reflectivity, excellent surface quality, and precision surface flatness to minimize scattering effects. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in a variety of standard sizes. TECHSPEC® Dual Band Laser Line Mirrors are ideal for beam steering applications in both laboratory and OEM laser systems. These mirrors are available in a 532/1064nm, 635-670/1064nm, and 800/1030nm dual band coating options for Nd:YAG lasers and red and green guide beams.