


[See all 8 Products in Family](#)

**TECHSPEC® 25.4mm Dia. x 76.2mm EFL, Enhanced Deep UV (DUV) 90° Off-Axis Mirror**



Ultraviolet Off-Axis Parabolic (OAP) Mirrors

Stock **#25-467** [CONTACT US](#)

- 1 + **A\$899<sup>20</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>A\$899.20</b> each
Qty 6-10	<b>A\$720.00</b> each
Qty 11-25	<b>A\$673.60</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Off-Axis Parabolic Mirror **Type:**

**Physical & Mechanical Properties**

76.20 **Y Offset (mm):**

25.40 +0.0/-0.1 **Diameter (mm):**

Surface Roughness ( $\text{\AA}$ ):

<50 RMS

## Optical Properties

Metal **Coating Type:**

Enhanced Aluminum (190-900nm) **Coating:**

90 **Off-Set Angle ( $^{\circ}$ ):**

190 - 900 **Wavelength Range (nm):**

76.20 **Effective Focal Length EFL (mm):**

Aluminum 6061-T6 **Substrate:**

**Coating Specification:**  
 $R_{\text{avg}} \geq 92\%$  @ 190 - 250nm  
 $R_{\text{avg}} \geq 83\%$  @ 250 - 900nm

$\pm 1$  **Focal Length Tolerance (%):**

38.1 **Parent Focal Length PFL (mm):**

$\lambda/8$  **Surface Figure, RMS:**

80-50 **Surface Quality:**

76.20 **Radius of Curvature (mm):**

$\lambda/4$  **Reflected Wavefront, RMS:**

## Threading & Mounting

[#47-111](#) **Compatible Mounting Plates:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **REACH 241:**


## Product Details

- Enhanced Metallic Coating for High Reflectivity Across Deep UV (DUV) and Visible Spectra
- 190nm Design Wavelength
- <50 $\text{\AA}$  RMS Surface Roughness

TECHSPEC® Ultraviolet Off-Axis Parabolic (OAP) Mirrors are coated with a DUV Enhanced Aluminum coating for excellent reflection from 190 – 900nm. To minimize scatter, these OAPs feature aluminum substrates and are diamond turned to have a surface roughness of <50 $\text{\AA}$  RMS. Standard imperial diameters are available with multiple focal length options which range from 25.4 – 203mm. TECHSPEC® Ultraviolet Off-Axis Parabolic Mirrors are ideal for use in DUV ellipsometers, DUV Raman spectroscopy, or for general focusing of UV light generated by broadband light sources. To facilitate mounting and system integration, threaded mounting plate [#47-111](#) (sold separately) which attaches to the base of these off-axis parabolic mirrors are available.

**Note:** The soft coating can be easily damaged by fingerprints and aerosols.

## Technical Information



## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

---

;