

[See all 72 Products in Family](#)

TECHSPEC® 25mm Dia. Linear Polarizing Film (XP42-40)



Stock #19-012 CLEARANCE **13 In Stock**

A\$24.⁸⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$24.80 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Note:
 Polarization axis can be identified as follows:
 Circular Parts - Parallel to direction of notch on polarizer
 Square Parts - Parallel to mark on protective film
 Rectangular Parts - Parallel to first listed dimension

Physical & Mechanical Properties

25.00 +0.0/-0.3 **Diameter (mm):**

0.40 ±0.05	Thickness (mm):
Polarizing Film	Construction:
Optical Properties	
9000:1 (nominal at 555nm)	Extinction Ratio:
Polymer Film XP42-40	Substrate: □
Single: 42 ±2 Parallel: 36.4 Crossed: <0.004 (nominal at 555nm)	Transmission (%):
400 - 700	Wavelength Range (nm):
>99.98 (nominal at 555nm)	Polarization Efficiency (%):
<±5	Transmission Variance after 1000 Hours (%):
Environmental & Durability Factors	
-40 to +80	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 235:

Product Details

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- [High-Temperature](#) Options Also Available



Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

Note: Polarizer Film with adhesive available.

Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

Technical Information



XP44 - Linear Polarizer

