

**TECHSPEC® 25mm Dia. x 75mm FL, NIR I Coated, Achromatic Lens**



Stock #22-493 **20+ In Stock**

[Other Coating Options](#)

- 1 + A\$233<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	A\$233.60 each
Qty 6-25	A\$187.20 each
Qty 26-49	A\$174.40 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Achromatic Lens **Type:**

**Physical & Mechanical Properties**

25.00 +0.0/-0.025 **Diameter (mm):**

24.00	<b>Clear Aperture CA (mm):</b>
<1	<b>Centering (arcmin):</b>
10.00 ±0.20	<b>Center Thickness CT (mm):</b>
6.00 ±0.10	<b>Center Thickness CT 1 (mm):</b>
4.00 ±0.10	<b>Center Thickness CT 2 (mm):</b>
7.98	<b>Edge Thickness ET (mm):</b>
Protective as needed	<b>Bevel:</b>

## Optical Properties

75.00	<b>Effective Focal Length EFL (mm):</b>
±1	<b>Focal Length Tolerance (%):</b>
69.06	<b>Back Focal Length BFL (mm):</b>
880.00	<b>Focal Length Specification Wavelength (nm):</b>
43.96	<b>Radius R<sub>1</sub> (mm):</b>
-42.90	<b>Radius R<sub>2</sub> (mm):</b>
-392.21	<b>Radius R<sub>3</sub> (mm):</b>
<a href="#">N-LAK22 / N-SF6</a>	<b>Substrate:</b> <input type="checkbox"/>
40-20	<b>Surface Quality:</b>
3.00	<b>f#:</b>
0.17	<b>Numerical Aperture NA:</b>
NIR I (600-1050nm)	<b>Coating:</b>
R <sub>avg</sub> ≤0.5% @ 600 - 1050nm	<b>Coating Specification:</b>
1.5λ	<b>Power (P-V) @ 632.8nm:</b>
λ/4	<b>Irregularity (P-V) @ 632.8nm:</b>
600 - 1050	<b>Wavelength Range (nm):</b>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 240:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Designed to Give Increased Resolution and Smaller Spot Sizes for NIR Wavelengths (750-1100nm)
  - Decreased Spherical Aberration for Monochromatic Sources Out to 2μm
  - Broadband AR Coating has <1% Reflectivity Between 750–1550nm
- TECHSPEC® Near-IR (NIR) Achromatic Lenses are designed to provide the smallest spot size possible for polychromatic light between 750 and 1100nm. By utilizing our NIR doublets instead of standard doublets designed for the

visible, the RMS spot diameter can be reduced from 43 $\mu\text{m}$  to 22.5 $\mu\text{m}$ , for example, when using polychromatic light. Spot size will be smaller when focusing on monochromatic sources. TECHSPEC Near-IR (NIR) Achromatic Lenses also reduce spherical aberration and perform superior when used with a monochromatic source up to 2 $\mu\text{m}$  in wavelength. Typical applications for these doublets include imaging lenses for the near infrared, focusing and expanding of NIR lasers, and focusing/collimating lenses for fiber optics and NIR LEDs.

## Technical Information

