

[See all 35 Products in Family](#)

**TECHSPEC® 25mm Diameter x 25mm FL, VIS Coated, K22R Plastic Aspheric Lens**



TECHSPEC® Plastic Aspheric Lenses

Stock #21-212 **14 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ **A\$116<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-24	<b>A\$116.80</b> each
Qty 25-99	<b>A\$83.20</b> each
Qty 100-249	<b>A\$60.80</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Aspheric Lens **Type:**

**Physical & Mechanical Properties**

25.00 ±0.15 **Diameter (mm):**

**Centering (arcmin):**

<5 (by design)	
21.5	Clear Aperture CA (mm):
1.07	Edge Thickness ET (mm):
7.40 ± 0.20	Center Thickness CT (mm):
Protective as needed	Bevel:
Convex	Shape of Back Surface:

## Optical Properties

25.00 @ 587.6nm	Effective Focal Length EFL (mm):
0.50	Numerical Aperture NA:
20.52	Back Focal Length BFL (mm):
Zeonex K22R	Substrate: <input type="checkbox"/>
587.6	Aspheric Design Wavelength (nm):
BBAR (425-675nm)	Coating:
R <sub>avg</sub> <0.7% @ 425 - 675nm	Coating Specification:
80-50	Surface Quality:
1.00	f#:
152.34	Radius R <sub>2</sub> (mm):
425 - 675	Wavelength Range (nm):
Infinite	Conjugate Distance:
587.60	Focal Length Specification Wavelength (nm):

## Environmental & Durability Factors

-30 to 70	Operating Temperature (°C):
-----------	-----------------------------

## Regulatory Compliance

<a href="#">Compliant</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	Reach 250:

## Product Details

- Full Prescription Data Available
  - Standard 25mm Diameter for Easy System Integration
  - High Numerical Aperture Designs for Superior Light Collection
- TECHSPEC® Plastic Aspheric Lenses offer a lightweight alternative to glass spherical or aspherical lenses. Designed with a standard 25mm diameter, these lenses can be easily integrated into most systems and applications using standard mounting hardware. The plastic substrate provides exceptional value while still maintaining excellent performance and a high numerical aperture. TECHSPEC® Plastic Aspheric Lenses feature low haze, low autofluorescence, and excellent coating adhesion, making these lenses ideal for OEM and research applications alike. For alternate designs or custom coating requirements, please contact our [Sales Department](#).

## Technical Information



