

TECHSPEC[®] 25mm UV-AR Coated and Aluminized, Fused Silica Penta Prism



Stock #49-023 CLEARANCE 20+ In Stock

-

1

+

A\$164^{.80}

ADD TO CART

Volume Pricing	
Qty 1+	A\$164.80 each
Need More?	Request Quote

Product Downloads

General

Type:

Penta Prism

Physical & Mechanical Properties

Dimensional Tolerance (mm):

±0.10

Bevel:

Protective as needed

Optical Properties

Coating:

UV-AR & Aluminized	
Substrate: ☐	
Fused Silica (Corning 7980)	
Surface Quality:	
20-10	
Angle Tolerance (arcmin):	
±1	
Image Orientation:	
Right-Handed	
Coating Specification:	
Entrance/Exit Faces: R _{abs} ≤1.0% @ 250 - 425nm, R _{avg} ≤0.75% @ 250 - 425nm, R _{avg} ≤0.5% @ 370 - 420nm Reflecting Surfaces: R _{avg} >85% @ 250 - 700nm w/Black Overpaint	
Ray Deviation (°):	
90	
Wavelength Range (nm):	
250 - 425	
Damage Threshold, By Design: ☐	
Entrance/Exit Faces: 3 J/cm2 @ 355nm, 10ns Reflecting Surfaces: 0.3 J/cm2 @ 532nm & 1064nm, 10ns	
Power (fringes) @ 632.8nm:	
0.20	
Irregularity (fringes) @ 632.8nm:	
0.20	


Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details


- Ray Deviation of 90°
- Right Handed Image
- Optical Tool for Defining a Right Angle
- Additional [Penta Prism](#) Options Available

Penta prisms are five-sided prisms featuring a ray deviation of 90° and a right handed image. The UV-AR coated options also have aluminized reflecting surfaces for increased efficiency. Slight movement of the prism does not affect the true right angle at which light rays are reflected, making a penta prism the ideal optical tool for defining a right angle in an optical system. TECHSPEC® UV Fused Silica Penta Prisms are made from UV fused silica which features low thermal expansion and excellent transmission throughout the UV, VIS, and NIR spectral ranges.


Technical Information




UV FS Transmission Curve




Right Angle Prism Ray Path




Right Angle Prism Ray Path




Right Angle Prism Tunnel Diagram



Right Angle Prism Tunnel Diagram




Penta Prism Ray Path



Penta Prism Tunnel Diagram

>

Stock No.	A	B
#49-016	5.00mm	6.10mm
#49-020		
#49-017	10.00mm	11.95mm
#49-021		
#49-018	20.00mm	21.65mm
#49-022		
#49-019	25.00mm	27.90mm



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).