

**TECHSPEC® 2.5X LS Series Area Scan Lens**



2.5XLS Series Area Scan Lens

Stock **#35-453** [CONTACT US](#)

⊖ 1 ⊕ **A\$6,206<sup>00</sup>**

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | <b>A\$6,206.00</b> each       |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

LS Series **Product Family:**

Window is included. Length includes window.  
Specifications are at primary magnification. **Note:**

Fixed Focal Length Lens **Type:**

No **Beamsplitter / Line Scan:**

**Special Type of Lens:**

**Physical & Mechanical Properties**

Variable Iris Option:

160.80 Length (mm):

75 Maximum Diameter (mm):

75 Outer Diameter (mm):

0 Maximum Rear Protrusion (mm):

529.00 Total Track (mm):

**Optical Properties**Horizontal Field of View @ Max Sensor Format:  
32.8mmField of View at Max Sensor Format:  
Horizontal: 26.3mm - 8.1°  
Vertical: 19.7mm - 6.1°  
Diagonal: 32.9mm - 10°

32.8mm Field of View, 82mm Sensor:

25mm Field of View, 62.5mm Sensor:

23.1mm Field of View, 57.7mm Sensor:

14.4mm Horizontal Field of View, 35mm Sensor:

11.7mm Horizontal Field of View, APS-H Sensor:

11.5mm Field of View, 28.7mm Sensor:

0.11 Numerical Aperture NA:

82.00 Maximum Image Circle (mm):

0.1099 Numerical Aperture NA, Object Side:

12 (7) Number of Elements (Groups):

117.00 Focal Length FL (mm):

2.35X - 2.65X Primary Magnification PMAG:

59.4 Working Distance (mm):

f/2.9 - f/22 Aperture (f#):

425 - 675 BBAR MS Coating:

425 - 675nm BBAR Coating Specification:

114.19 Entrance Pupil Position (mm):

95.83 Object Space Principal Plane (mm):

-77.27 Image Space Principal Plane (mm):

0.01 Maximum Distortion (%):

&gt;98% Relative Illumination:

-61.01 Exit Pupil Position (mm):

VIS Lens Wavelength Range:

**Sensor**

82mm Optimized Sensor Format:

82mm (Image Circle) Maximum Sensor Format:

---

5.00 Pixel Size (µm):

## Threading & Mounting

N/A Filter Thread:

75 Mounting Diameter (mm):

V-70 Mbunt Mount:

## Regulatory Compliance

[View](#) Certificate of Conformance:

---

## Product Details

- 82mm Line Scan (LS), V-70 Mount
- Up to 16k, 5µm Pixel Size Line Scan Sensors
- High Resolution, Low Distortion, Uniform Field Performance
- 1.65X to 2.65X Primary Magnification

TECHSPEC® LS Series Line Scan Fixed Focal Length Lenses are low distortion lenses designed for 82mm 16k line scan cameras with 5µm pixels and 62.5mm 12k line scan cameras with 5µm pixels. For coaxial inline illumination, these lenses are available with a beamsplitter for line scan sensors or with a window for area scan sensors. The locking iris is adjustable from f/2.9 to f/22, while the V-Mount provides ease of adjustment and alignment. The uniform and high resolution performance across the entire image makes the TECHSPEC® LS Series Line Scan Fixed Focal Length Lenses ideal for applications such as electronics, flat panel display and semiconductor wafer inspections.