


[See all 7 Products in Family](#)

3X Mitutoyo Telecentric Objective

See More by [Mitutoyo](#)



3X (#56-985) & 5X (#56-986)



Stock **#56-985** **4 In Stock**

A\$2,344.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$2,344.00 each
Need More?	Request Quote

Product Downloads

General

375-037-1 **Model Number:**

Microscope Objective **Type:**

Finite Conjugate **Style:**

Manufacturer:

Note:

Image is formed 280mm from specimen (170mm from the mounting flange)

Physical & Mechanical Properties

33.00 Length (mm):

33.00 Length excluding Threads (mm):

30 Maximum Diameter (mm):

55 Weight (g):

Optical Properties

2.10mm Horizontal Field of View, 1/2" Sensor:

2.90mm Horizontal Field of View, 2/3" Sensor:

58.51 Focal Length FL (mm):

NA0.09 Aperture (f/#):

3X Magnification:

0.09 Numerical Aperture NA:

3.06 Resolving Power (μm):

34.00 Depth of Field (μm):

8 Field of View, 24 Diameter Field Eyepiece (mm):

6 Field of View, 18 Diameter Field Eyepiece (mm):

77 Working Distance (mm):

435 - 655 Wavelength Range (nm):

110 Parfocal Length (mm):

N/A Immersion Liquid:

11.00 Maximum Image Circle (mm):

Sensor

2/3" Maximum Sensor Format:

Threading & Mounting

M26 x 36 TPI Mount:

M26 x 36 TPI Mounting Threads:

Environmental & Durability Factors

+5 to +40 Operating Temperature ($^{\circ}\text{C}$):

20 - 80% Operating Humidity:

Regulatory Compliance

[Exempt](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Contains SVHC\(s\)](#) REACH 241:

Product Details

- Long Working Distances Allow for Integration into Machine Vision Measurement Systems
- Compact Design and Long Parfocal Length Simplifies Mounting
- [Tube](#) Available for Use with C-Mount Cameras
- Aluminum Alloy Housing

Mitutoyo Telecentric Objectives are ideal for high-resolution, high power machine vision measurement and optical gauging systems. With powers up to 100X, these objectives can be used for semiconductor production and inspection, and in metrology, quality assurance, and R&D laboratories. These objectives are constructed of an aluminum alloy housing. Mitutoyo Telecentric Objectives have a compact design and a long parfocal length that simplifies mounting. They are easily integrated into C-Mount imaging systems with our Mitutoyo C-Mount Camera Tube [#56-992](#).

Edmund Optics is the main source for Mitutoyo Objectives. Place your orders now for these in demand quality products.

Technical Information

Magnification	A	B	C	D	E	Stock No.
1X	49	10	16.5	31.5	31.5	#56-984
3X	33	10	18	25	28	#56-985
5X	49	10	17	25	28	#56-986
10X	59	10	14.5	30	30	#56-987
20X	90	14.5	23	33	39	#87-228
50X	97	14.7	23	33	39	#87-229
100X	104	14.1	23	33	39	#87-230

