

TECHSPEC<sup>®</sup> 40mm, Metric Micrometer Z-Stage



TECHSPEC<sup>®</sup> Vertical Translation Stages



[+1](#)

Stock **#66-501** 5 In Stock

-

1

+

A\$1,248<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-2        | A\$1,248.00 each              |
| Qty 3+         | A\$1,087.20 each              |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Metric

Type:

Physical & Mechanical Properties

Linear (Z)

Type of Movement:

Guide System:

|                        |                              |
|------------------------|------------------------------|
| Crossed Roller Bearing |                              |
| 40 x40                 | Stage Size (mm):             |
| 10                     | Travel (mm):                 |
| M6 x1                  | Center Hole:                 |
| Aluminium Stage        | Construction:                |
| 0.5                    | Leadscrew Pitch (mm):        |
| 2                      | Load Capacity (kg):          |
| 1.57 x 1.57            | Stage Size (inches):         |
| 3                      | Straight Line Accuracy (µm): |

## Hardware & Interface Connectivity

| Metric Micrometer | Type of Drive: |
|-------------------|----------------|
|                   |                |

## Threading & Mounting

**Mounting Threads:**  
(1) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4

## Regulatory Compliance

|                                  |                                    |
|----------------------------------|------------------------------------|
| <a href="#">Exempt</a>           | <b>RoHS 2015:</b>                  |
| <a href="#">View</a>             | <b>Certificate of Conformance:</b> |
| <a href="#">Contains SVHC(s)</a> | <b>REACH 241:</b>                  |

## Product Details

**Bottom adapter plates**, sold separately, are required to mount 30mm and 40mm stages to standard breadboards.

- Mechanically Compatible with our **TECHSPEC® Stages**
- Fine Micrometer Movement
- Locking Screw on Stages

Our newly developed precision TECHSPEC® Vertical Translations Stages (Z-axis stages) feature a unique and advanced crossed roller bearing guide system that provides high accuracy, rigidity and load capacity. Each stage is designed to integrate with our line of [TECHSPEC® stages](#) in order to provide flexibility in allowing the user to create a number of multi-axis configurations. These stages have a locking screw and fine micrometer movement. TECHSPEC® Vertical Translations Stages are constructed of aluminum and have a linear (Z) movement. The stages are available in both English and Metric versions and are offered in four sizes.

## Technical Information

