

[See all 36 Products in Family](#)

## 500nm, 6 x 6mm, OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock #15-200 **20+ In Stock**

⊖ 1 ⊕ A\$80.<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | A\$80.00 each                 |
| Qty 10-25      | A\$72.00 each                 |
| Qty 26-49      | A\$67.20 each                 |
| Need More?     | <a href="#">Request Quote</a> |

### Product Downloads

### General

Longpass Filter **Type:**

### Physical & Mechanical Properties

6.00 x 6.00 +0.00/-0.20 **Dimensions (mm):**

6.00 **Length (mm):**

|                            |                             |
|----------------------------|-----------------------------|
| 2.00 ±0.10                 | <b>Thickness (mm):</b>      |
| 6.00                       | <b>Width (mm):</b>          |
| 90                         | <b>Clear Aperture (%):</b>  |
| ML-C-48497A, Section 3.4.1 | <b>Physical Durability:</b> |

## Optical Properties

|                   |  |
|-------------------|--|
| 0                 | <b>Angle of Incidence (°):</b>             |
| ≥2.0              | <b>Optical Density OD (Average):</b>       |
| 500.00 ±10        | <b>Cut-On Wavelength (nm):</b>             |
| <b>BOROFLOAT®</b> | <b>Substrate:</b> <input type="checkbox"/> |
| Hard Coated       | <b>Coating:</b>                            |
| 200 - 475         | <b>Rejection Wavelength (nm):</b>          |
| 60-40             | <b>Surface Quality:</b>                    |
| ≥85               | <b>Transmission (%):</b>                   |
| 525 - 1600        | <b>Transmission Wavelength (nm):</b>       |
| 200 - 1600        | <b>Wavelength Range (nm):</b>              |

## Environmental & Durability Factors

|                            |                                  |
|----------------------------|----------------------------------|
| ML-STD-810F, Section 507.4 | <b>Environmental Durability:</b> |
|----------------------------|----------------------------------|

## Regulatory Compliance

|                  |                                    |
|------------------|------------------------------------|
| <b>Compliant</b> | <b>RoHS 2015:</b>                  |
| <b>View</b>      | <b>Certificate of Conformance:</b> |
| <b>Compliant</b> | <b>Reach 253:</b>                  |

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Sharp Cut-On Wavelength
- ≥85% Transmission and OD 2.0 Blocking
- 6mm Square or 12.5/25mm Diameter Sizes
- **TECHSPEC® OD 4.0 Longpass Filters** Also Available

OD 2.0 Longpass Filters are cost-effective filters with cut-on wavelengths ranging from 400 to 950nm. These longpass filters provide ≥85% transmission across a transmission band that extends out to 1600nm while providing OD 2.0 blocking across their rejection band. The back surface of each filter is coated with an antireflection (AR) coating, increasing the overall efficiency of the filter. OD 2.0 Longpass Filters can be combined with OD 2.0 Shortpass Filters to create custom bandpass filters to meet application requirements in the visible or near-infrared. These longpass filters are ideal for use in fluorescence applications or separating spectral orders, with the 6 x 6mm sized filters suitable for integration into optical instrumentation requiring cost-effective, lightweight filters.

## Technical Information

### OD 2.0 Longpass Filters



### Compatible Mounts

;